## **BASIN TAP WA200**



## Ø 52 x 171 x 155 mm

Low pressure

- Single-lever basin tap without waste fitting in robust, germ-reducing and easy-care stainless steel (AISI 303).
- Version: low pressure, suitable for unpressurised tanks. Operating pressure 2–6 bar.
- Solid stainless steel body; visible surfaces satin finished. Further available surfaces: see below.
- High quality ceramic mixer cartridge with adjustable temperature limit setting (scald protection).
- Neoperl<sup>®</sup> air bubble spray M21 x 1 mm.

Design height:	171 mm
Outlet height:	87 mm
Projection:	98 mm
Length of lever:	40 mm

- Wear parts can be replaced as modules.
- Installation dimensions: Ø 33-40 mm Surface thickness max. 40 mm
- Mounting: With one counternut.
- Delivery includes fixing material and three flexible connecting hoses clad in stainless steel.
- Weight, including single package: 1.4 kg

## Suggested text for specifications:


Single-lever basin tap in stainless steel (AISI 303) for counter mounting. Version: low pressure. Solid stainless steel body; visible surfaces satin finished. Ceramic mixer cartridge with adjustable temperature limit setting. Delivery includes fixing material and three flexible connecting hoses clad in stainless steel.

Dimensions: Ø 52 x 171 x 155 mm Outlet height 87 mm Projection 98 mm Length of lever 40 mm

Article No. WA200

Available surfaces	ID No.
satin finished (standard)	924 267
highly polished	931 267





EW

## Ernst Wagner GmbH & Co. KG Ernst-Abbe-Straße 21 · D-72770 Reutlingen · Tel.: +49712151539-0 · Fax: -20 info@wagner-ewar.de · www.wagner-ewar.de